



DLPLC-YTHH2 Liquid Mix Training Set

■ Overview

- The system is composed of mixing device and material storage. Both liquids are transferred to mixing device as required; The stirring motor driven stirring impeller rotate to mix the liquid. There is a solenoid valve on the below end of the mixing device which control mixed liquid flow to storage device.

■ Technical Parameter

- Total dimension: 680×450×560mm
- Input power: DC 24V
- Capacity: < 500VA

■ Optional

- Mitsubishi PLC module (analog)
- Siemens PLC module (analog)
- Computer, PC software
- HMI module